

Remote control set

Remote control set

(only possible with lamps with LED technology)

The lamps are normally operated by an external footswitch (against a surcharge).

As an alternative we can also provide a **remote control unit**, which is charged extra. The remote control unit incorporates a transmitter with which you can switch all the LED lamps on and off (max. 6 lamps / max. 15 W). The footswitch is no longer needed when a remote control unit is included.

The remote control set consists of:

- 1 transmitter
- 1 receiver
- 1 LED EVG 12 V DC/15 W

Remote control unit	
Set for LED lamps	
3333	127.00

IR repeater set

IR repeater set

Infrared signal transmission set for operating media units behind wooden/high-gloss fronts. You can operate as many media units as you like in one compartment with one set. The following applies:

- At least 4 cm distance between unit and front
- One set must be used for each compartment
- The transmitter must be placed in the immediate vicinity of the receiver eye of the media unit
- High-frequency signals cannot be transmitted

The IR repeater set consists of:

- 1 receiver eye (Ø 3.0 cm) incl. standing bracket (4.2 x 5.5 x 3.0 cm)
- 1 electric transmitter
- 1 plug EVG 12 V
- Cable clamps

Infrared repeater set	
for TV units (1 set per compartment)	
7777	113.00

Base frames and mattress

Base frames, mattress




Base frame, 200 cm long				Base frame, 200 cm long				Mattress, 200 cm long						
80	90	120	140	80	90	120	140	80	90	140	160	180		
fixed				head and foot section adjustable				Interior sprung mattress						
8282	8292	8222	8242	8082	8092	8022	8042	8820	8920	1424	1624	1824		
198.00	198.00	260.00	315.00	342.00	342.00	411.00	473.00	590.00	590.00	859.00	968.00	1075.00		

Important notes on ordering:

Wood versions:

You can choose from different wooden surface versions. Please always remember to state the model number of the required wood surface version in your order.



Wood versions for wooden sections

Model no. Versions

1002	Natural oak
1008	Core walnut
1007	Light brown ash
1009	White lacquer

Important notes on ordering:

Wood versions:

You can choose from different wooden surface versions. Please always remember to state the model number of the required wood surface version in your order.



Wood versions for ancillary table

Model no. Versions

1001	Oak anthracite
1002	Natural oak
1003	Oak mocca
1004	Walnut
1006	Polar-white lacquer

Armboard, backboards, trays

Please be sure to state the model number of the required wood version when ordering armboards, backboards and trays (see list of versions above)!

Armboard Backboard



Article	Armboard		Backboard		Backboard	
	60 x 87 x 30		38 x 87 x 30		38 x 120 x 30	
HxWxD in cm	Order no.	RRP*	Order no.	RRP*	Order no.	RRP*
Order no./RRP*	219120	549.00	219620	480.00	219220	549.00

Trays



Article	Tray		Tray		Tray	
	4 x 86 x 51		4 x 86 x 35		4 x 48 x 20	
HxWxD in cm	Order no.	RRP*	Order no.	RRP*	Order no.	RRP*
Order no./RRP*	219050	232.00	219030	205.00	219040	136.00

Ancillary table

Please be sure to state the model number of the required wood version when ordering ancillary tables (see list of versions above)!



Article	Ancillary table	
	48 x 40 x 67	
HxWxD in cm	Order no.	RRP*
Order no./RRP*	119010	542.00

NEW









Quality of walls / assembly instructions

Important notes:

The quality of the wall must be checked carefully by qualified personnel before assembly takes place.



Units must only be assembled by qualified personnel who carefully observe the assembly instructions.

The plastic plugs with the type number PSD-SL 8x90 from the Tox company which are supplied by hülsta are suitable when the quality of the wall and the pressure resistance levels comply with the table below. Under no circumstances can units be fitted on light masonry.

	Concrete	>= C20/25	Pressure resistance >= 20 N/mm ²	DIN 1045/1 ETAG 001		Vertically perforated brick	Hiz 12	Pressure resistance >= 10 N/mm ²	DIN 105-1
	Concrete and solid brick	Mz 12	Pressure resistance >= 12 N/mm ²	DIN 105 DIN EN 771-1		Perforated brick with high density	PNE	Pressure resistance >= 10 N/mm ²	Z-17.1-636
	Solid sand-lime brick	KS 12 KSL 12	Pressure resistance >= 12 N/mm ²	DIN 106 DIN EN 771-2		Precision blocks	ST 9	Pressure resistance >= 10 N/mm ²	DIN 105-1
						Perforated sand-lime brick			
						Solid brick with porous density		Pressure resistance >= 2,5 N/mm ²	

We also supply mounting sets with compound mortar from the Tox company for the following types of walls.

Again, units must only be assembled by qualified personnel who carefully consider the quality of the wall and observe the assembly instructions. The pressure resistance levels stated must be adhered to at all times.

	Perforated brick and vertically perforated brick	Pressure resistance >= 4 N/mm ²
	Hollow blocks with light concrete	Pressure resistance >= 2 N/mm ²

Mounting sets and the matching dispensing gun

Dispensing gun
A dispensing gun must be ordered once with each mounting set.

Mounting set 1
incl. special mounting materials such as screws and plugs as well as mortar compound; suitable for 140 cm wide wall units (with 3 wall mounting points)

Mounting set 2
incl. special mounting materials such as screws and plugs as well as mortar compound; suitable for 210 cm wide wall units (with 4 wall mounting points)



Dispensing gun		Set 1		Set 2	
Order no.	RRP*	Order no.	RRP*	Order no.	RRP*
2222	40.00	5555	67.00	8888	81.00

It is essential for qualified personnel to choose a different and more suitable mounting method in all other cases. hülsta cannot be held responsible for the technically correct choice of different mounting methods!